




updated 14.4.2021

Lappset - Maintenance Paints





MAINTENANCE INSTRUCTIONS

Maintenance for wooden parts

General principle is, that there will be chosen same type of paint as in original treatment.

Lappset delivers maintenance paint for wooden parts in 1 litre, but you are also able to purchase similar product from your local hardware store according to the closest RAL code.

Follow the instructions for painting conditions, given by paint manufacturer.

Preparations



- 1. Clean surfaces with brush.
- 2. Wash surfaces with paint remover.
- 3. Wash possible molded surfaces with hypochlorite solution for mould removal.
- 4. Rinse the surfaces carefully with clean water, from above downwards, e.g. with spray
- 5. Remove old paint.
- 6. Sand clean and dry surface (sandpaper 240-280) and remove sanding dust.

If you are not sure, which paint or treatment you should choose, please contact our customer service or your local Lappset representative.



FINNO, FITNESS, STREETWORKOUT & SENIOR SPORT


Check what year your product was shipped and select correct maintenance paint / treatment according to table.

	02102-1-1-0-10-1-1-0-10-1-1-0-10-1-1-0-10-1-0-10-1									
H	ł	H		Posts and	d beams					
T	P	P	1A	Colour	Original paint closest to*	Description of used treatment	Lappset order code 1 I.			
Х				Dark brown	no RAL code available	Matt cover paint	911782			
Х				Brown	no RAL code available	Matt cover paint	911784			
Х				Grey	no RAL code available	Matt cover paint	911786			
	Х			Dark brown	no RAL code available	Tone wood stain/oil	910716			
	Х			Brown	no RAL code available	Tone wood stain/oil	910715			
	Х			Grey	no RAL code available	Tone wood stain/oil	910717			
		Х		Dark brown	RAL 8019	Semi-matt cover paint	916585			
		Х		Brown	RAL 8024	Semi-matt cover paint	916928			
		Х	Х	Grey	RAL 7042	Semi-matt cover paint	911101			
			Х	Brown	RAL 8002	Semi-matt cover paint	911112			
			Х	Red	RAL 3011	Semi-matt cover paint	911103			
			Х	Yellow	RAL 1011	Semi-matt cover paint	911102			
			Х	Green	RAL 6020 or RAL 6028	Semi-matt cover paint	911117			

* Please note, presented RAL codes are only references of the original shade used.



Finno products launched in 2014



Finno products before 2014



ຳ (je je								
I.	R	Walls and other wooden and plywood parts (cover paints)							
11		Colour	Original paint closest to*	Description of used paint	Lappset order code 1 I.				
Х		Dark grey	RAL 7024	Cover paint	917681				
Х		Light grey	RAL 7040	Cover paint	917680				
Х		Red	RAL 3020	Cover paint	911167				
Х		Blue	RAL 640-2	Cover paint	917678				
Х		Green	RAL 6018	Cover paint	914949				
Х		Yellow	RAL 1003	Cover paint	917679				
Х		Lime green	RAL 250-3	Cover paint	917682				
Х		Fuchsia	RAL 4006	Cover paint	917683				
	Х	Red	RAL 3002	Cover paint	911163				
	Х	Blue	RAL 5015	Cover paint	911169				
	Х	Yellow	RAL 1007	Cover paint	911162				
	Х	White	RAL 9010	Cover paint	911115				
	Х	Green	RAL 6032	Cover paint	911127				
	Х	Orange	RAL 2000	Cover paint	911146				
	Х	Black	RAL 9017	Cover paint	911137				
	Х	Ligh brown	RAL 1011	Cover paint	911111				
	Х	Grey	RAL 7004	Cover paint	911114				
	Х	Brown	RAL 8015	Cover paint	911134				

* Please note, presented RAL codes are only references of the original shade used.





Senior Sport



FLORA PRODUCTS

Check what year your product was shipped and select correct maintenance paint / treatment according to table.

//	, (502),	1.2. <0.20 1.2. <0.2	13- 1018- 1020			
合町		H	Posts, t	Posts, beams, walls and other brown wooden part		
4.	4.	4.	Colour	Original treatment	Maintenance	Order code 1 l.
Х			Brown	Covering wood stain	Matt cover paint	911790
	Х		Maroon	Covering wood stain	Matt cover paint	911788
		Х	Brown	Tone wood stain	Tone wood stain/oil	910714
			X Brown	Semi-transparent oil	Wood oil	911110

HALO PRODUCTS

		Posts and beams								
	Colour	Description of used tone varnish	Maintenance	Order code 1 I.						
6	Beige	Tone varnish	Tone varnish	919145						

HALO CUBIC PRODUCTS

Check what year your product was shipped and select correct maintenance paint / treatment according to table.

~~	1202,1		120- C2)								
			Posts and	Posts and beams							
			Colour	Original treatment	Maintenance	Order code 1 I.					
Х			Brown	Covering wood stain	Matt cover paint	911790					
	Х		Maroon	Covering wood stain	overing wood stain Matt cover paint						
		Х	Brown	Tone wood oil	Tone wood stain	910714					

















PAINTED PARK FURNITURE

	Colour	Description of used tone varnish	Maintenance	Order code 1 l.
6	Teak red	10958/19	Futura Aqua 40	910975
6	Grey	TM 7426/08	Helo Aqua 40	919140
6	Green	10960/19	Futura Aqua 40	910977
6	Light brown	10957/19	Futura Aqua 40	910974
6	Dark brown	10957/19	Futura Aqua 40	910976





OILED PARK FURNITURE

Preparations for oiled furniture

- 1. Clean surfaces with brush.
- 2. Wash surfaces with water, you can also use mild detergent (no bleach).
- 3. Wash possible molded surfaces at the same time.
- 4. Rinse the surfaces carefully with clean water (using a hose, no pressure cleaner) and let it dry before oiling.


Please find suitable wood oil from your local hardware store.

JATOBA FURNITURE

Colour	Description of used oil	Maintenance	
Light brown	Linseed oil	Wood oil	~ F

LINAX TREATED FURNITURE

	Colour	Description of used oil	Maintenance	Unt
6	Clear	Linseed oil	Linseed oil	Dort





MAINTENANCE INSTRUCTIONS

Maintenance for painted metal parts


The original surface treatment used for the metal parts is polyester powder paint.

Description of maintenance paint: Surface treatment for metal. Car paints can be used as an alternative surface treatment.

Lappset delivers some maintenance paints for metal parts in 0,3 litre containers, but you are also able to purchase similar products from your local harware store according to the closest RAL code.

Follow the instructions for painting conditions, given by paint manufacturer.

Maintenance paints for metal parts are intended to be used as touch-up paint for scratches and minor defects in surface. Paints are not intended for oversprayings of large areas.



If you are not sure, which paint or treatment you should choose, please contact our customer service or your local Lappset representative.



PLAY EQUIPMENT

		Colour	Original paint closest to *	The colour ref. of the product being maintained **	Lappset order code for 300 ml.
	Metal swings Cloxx	Dark grey	RAL 7024		not provided
	Metal swings Cloxx	Light grey	RAL 9023		not provided
	Metal parts in wooden Play products 2013-	Grey shimmer	RAL 9022		not provided
previous version	Metal parts in wooden Play products 2007 - 2013	Grey	RAL 7037	-212	908028***
previous version	Metal parts in wooden Play products - 2007	Red	RAL 3000	-206	908031

SPORT EQUIPMENT

			Colour	Original paint closest to *	The colour ref. of the product being maintained **	Lappset order code for 300 ml.
	Fitness, Street workout and Senior Sport products (Theme: Active) Basket ball stands		Turqoise	RAL 690-2	-215	908032
	Fitness, Street workout and Senior Sport products (Theme: Solid)	6	Grey shimmer	RAL 9022		not provided
	Fitness, Street workout and Senior Sport products (Theme: Slow) Gym products Basket ball stands		Lime green	RAL 250-3	Gym products: -217	908033
	Fitness, Street workout and Senior Sport products (Theme: Joy)		Pink	RAL 4003	-218	908034
	Gym products Goals	\bigcirc	White	RAL 9010	Gym products: -214	not provided
	Gym Basket ball stands		Dark grey	RAL 7024	Gym products: -205	908029
previous version	Senior Sport products before 2016		Red	RAL 3000	-206	908031



PARK FURNITURE

		Colour	Original paint closest to*;	The colour ref. of the product being maintained**	Lappset order code for 300 ml.
NF-products, Park products with 060-		Black	RAL 9005	060xxx-99	908030
NF-products Park products with 060- CL and CT Litterbins		Dark green	RAL 6012	060xxx-17, 060xxx-79, CLxx-6012, CTxx-6012	not provided
NF-products Park products with 060- CL and CT Litterbins		Dark grey	RAL 7024	060xxx-1, 060xxx-78, CLxx-7024, CTxx-6012	908029
NF-products	6	Grey	RAL 7042		908027***
NF-products	6	Dark grey	RAL 7016		not provided
NF-products	6	Dark green	RAL 6007		not provided
Park products with 060-		Beige	RAL 1015	060xxx-16, 060xxx-80	not provided
NF-bollard rings		Red	RAL 3020		not provided
NF-bollard rings	6	Light blue	RAL 6027		not provided
NF-bollard rings		Orange	RAL 2008		not provided
NF-bollard rings	6	Olive green	RAL 6021		not provided
NF-bollard rings		Mustard	RAL 1004		not provided
NF-bollard rings		Green	RAL 6017		not provided

* Please note, presented RAL codes are only references of the original shade used.

** Not all products have had a colour spesification code at the end of the product number. In these cases, please see the the installation instructions to find the right colour.

*** Maintenance paint colour is not exact match with original color, because the original colour is a metallic colour and is not available as maintenance paint.

